

Lens Materials


1.74

1.67

1.60

1.53

1.50



The above diagrams are for indication purposes only.

Lens Materials

1.74
NULUX
 IDENTITY V+

1.67
HILUX
 TRUEFORM

1.60
NULUX
 TRUEFORM

1.53
NULUX
 TRUEFORM

1.50
HILUX
 TRUEFORM

Power	1.74 NULUX IDENTITY V+	1.67 HILUX TRUEFORM	1.60 NULUX TRUEFORM	1.53 NULUX TRUEFORM	1.50 HILUX TRUEFORM
+6.00	CT: 4.1 mm - ET: 0.8 mm - Wt: 9.9 g	CT: 4.5 mm - ET: 0.8 mm - Wt: 10.1 g	CT: 5.0 mm - ET: 0.8 mm - Wt: 10.8 g	CT: 6.1 mm - ET: 0.8 mm - Wt: 11.0 g	CT: 6.5 mm - ET: 0.8 mm - Wt: 14.1 g
+4.00	CT: 3.0 mm - ET: 0.8 mm - Wt: 7.7 g	CT: 3.2 mm - ET: 0.8 mm - Wt: 7.5 g	CT: 3.7 mm - ET: 0.8 mm - Wt: 8.5 g	CT: 4.3 mm - ET: 0.8 mm - Wt: 8.1 g	CT: 4.5 mm - ET: 0.8 mm - Wt: 10.0 g
+2.00	CT: 1.9 mm - ET: 0.8 mm - Wt: 5.5 g	CT: 2.0 mm - ET: 0.8 mm - Wt: 5.3 g	CT: 2.3 mm - ET: 0.8 mm - Wt: 5.9 g	CT: 2.5 mm - ET: 0.8 mm - Wt: 5.1 g	CT: 2.7 mm - ET: 0.8 mm - Wt: 6.7 g
-2.00	CT: 1.0 mm - ET: 2.3 mm - Wt: 8.2 g	CT: 1.0 mm - ET: 2.5 mm - Wt: 7.9 g	CT: 1.0 mm - ET: 2.7 mm - Wt: 8.2 g	CT: 1.3 mm - ET: 3.7 mm - Wt: 9.6 g	CT: 2.0 mm - ET: 4.9 mm - Wt: 17.3 g
-4.00	CT: 1.0 mm - ET: 3.8 mm - Wt: 11.8 g	CT: 1.0 mm - ET: 4.0 mm - Wt: 11.4 g	CT: 1.0 mm - ET: 4.4 mm - Wt: 11.9 g	CT: 1.3 mm - ET: 5.6 mm - Wt: 12.3 g	CT: 2.0 mm - ET: 8.0 mm - Wt: 24.3 g
-6.00	CT: 1.0 mm - ET: 5.4 mm - Wt: 15.8 g	CT: 1.0 mm - ET: 5.7 mm - Wt: 15.1 g	CT: 1.0 mm - ET: 6.3 mm - Wt: 15.9 g	CT: 1.3 mm - ET: 7.7 mm - Wt: 16.1 g	CT: 2.0 mm - ET: 11.1 mm - Wt: 31.5 g
-8.00	CT: 1.0 mm - ET: 6.5 mm - Wt: 18.5 g	CT: 1.0 mm - ET: 7.5 mm - Wt: 19.0 g	CT: 1.0 mm - ET: 8.3 mm - Wt: 20.2 g	CT: 1.3 mm - ET: 10.2 mm - Wt: 20.3 g	CT: 2.0 mm - ET: 12.2 mm - Wt: 29.7 g

- 3 times stronger than 1.50
- Abbe value of 31
- Ideal for prescriptions of -5.00 to +5.00 & above
- No limitations in frame choice

- 5 times stronger than 1.50
- Abbe value of 31
- Ideal for prescriptions of -4.00 to +4.00 & above
- Aesthetically good in a rimless / supra mount

- 4 times stronger than 1.50
- Abbe value of 41
- Ideal for prescriptions up to -5.00 to +5.00
- Great optical performance

- 3 times stronger than 1.50
 - Abbe value of 43
 - Ideal for prescriptions up to -5.00 to +5.00
 - Ideal for children
- 2 year guarantee on PNX 1.53 lenses against cracking or breaking of the lens. The damaged lens will be replaced by Hoya with a lens of the same parameters. No credit note available.

- 50% lighter than glass
- Abbe value of 58
- Ideal for prescriptions up to -2.00 to +2.00
- Cost effective

Notes: _____

Notes: _____

Notes: _____

Notes: _____

Notes: _____

Please note: All data quoted for Minus Powers is for 65mm diameter lenses, and all data quoted for Plus Powers is for 60mm diameter lenses. The above diagrams are for indication purposes only.